

Dodatni pribor za nape, 538 mm DSZ4660



- V kombinaciji z podvgradnimi napami
- Okvir za skrito vgradnjo omogoča nevidno vgradnjo nape v visečo omarico
- Za montažo na kuhinjski steni
- Ustreza vgradnim izvlečnim napam širine 60 cm

Tehnični podatki

Mere embalaranega izdelka:90x530x640 mm
Dimenzija palete: 150.0 x 80.0 x 120.0
Standardno število enot na paleto: 30
Neto masa: 2.9 kg
Bruto masa: 5.0 kg
EAN koda:4242002882390



4 242002 882390




Dodatni pribor za nape, 538 mm DSZ4660

Dokupni pribor


- V kombinaciji z podvgradnimi napami
- Okvir za skrito vgradnjo omogoča nevidno vgradnjo nape v visečo omarico
- Za montažo na kuhinjski steni
- Ustreza vgradnim izvlečnim napam širine 60 cm

Dodatni pribor za nape, 538 mm DSZ4660




Dimenzije v mm

measurements in mm



Fitting the telescopic hood with lowering frame
Fitting directly to the kitchen wall




Montaža aparata
s spustljivim okvirjem

* glejte razpredelnico s kombinacijami

Dimenzije v mm

Dimenzije v mm

**Montaža vgradne izvalne nape s
kompletom za recirkulacijo zraka in
okvirjem za skrito vgradnjo**




A: Glejte preglednico za kombiniranje

measurements in mm
Combination table for 60 cm telescopic hood with lowering frame

Design of the appliance in the cupboard	Appliance installation depth with lowering frame	Depth of the handle strip (X)	Overall installation depth	Kitchen unit carcass depth
Design A	301	17	318	≥ 320
	301	20	321	≥ 323
	301	32	333	≥ 335
Design B	301	32	333	≥ 335


When using recess panelling of >5 mm, the lowering frame must be supported from below.
The kitchen unit carcass depth must be adjusted accordingly.

measurements in mm
Design A




Fitting the telescopic hood with lowering frame – kitchen unit carcass depth as per combination table

measurements in mm
Design B



Fitting the telescopic hood with lowering frame – kitchen unit carcass depth as per combination table

Dimenzije v mm
Montaža vgradne izvlečne nape s kompletom za recirkulacijo zraka in okvirjem za skrito vgradnjo



A: Menjava filtra